

Aspire Hand Made Pressure Reducing Seat



- Handmade pressure reducing seat
- Special foam design, engineered to improve the spread of pressure across the seat compliments users pressure management routine
- Waterproof but breathable anti-microbial four-way stretch Dartex material to optimises user comfort
- Independently tested and proven to be effective in reducing pressure levels
- Seat height: 65 mm

Warranty Information

- 1 Year



✓ Contracted DVA product

✓ Contract approved

ndis

Item Code:

05_093330084_0103_1_2

Mobile Shower Commode –

Composite: 05_413_0103_1_2

Click [here](#) for more information

Compliance

AS/NZS 3973:2009

| Code | Display Name | Seat Depth | Seat Width |
|-----------|---|------------|------------|
| BTC089122 | Pressure Reducing - Open Front - 320 mm | 320 mm | 320 mm |
| BTC089124 | Pressure Reducing - Closed Front - 320 mm | 320 mm | 320 mm |
| BTC089126 | Pressure Reducing - Open Front - 400 mm | 400 mm | 400 mm |
| BTC089128 | Pressure Reducing - Closed Front - 400 mm | 400 mm | 400 mm |
| BTC089130 | Pressure Reducing - Open Front - 460 mm | 460 mm | 460 mm |
| BTC089140 | Pressure Reducing - Closed Front - 460 mm | 460 mm | 460 mm |

| Code | Display Name | Seat Depth | Seat Width |
|-----------|---|------------|------------|
| BTC089150 | Pressure Reducing - Open Left - 460 mm | 460 mm | 460 mm |
| BTC089160 | Pressure Reducing - Open Right - 460 mm | 460 mm | 460 mm |
| BTC089170 | Pressure Reducing - Open Front - 500 mm | 430 mm | 500 mm |
| BTC089180 | Pressure Reducing - Closed Front - 500 mm | 430 mm | 500 mm |
| BTC089190 | Pressure Reducing - Open Front - 550 mm | 460 mm | 550 mm |
| BTC089200 | Pressure Reducing - Closed Front - 550 mm | 460 mm | 550 mm |
| BTC089210 | Pressure Reducing - Open Front - 600 mm | 470 mm | 600 mm |
| BTC089220 | Pressure Reducing - Closed Front - 600 mm | 470 mm | 600 mm |
| BTC089230 | Pressure Reducing - Open Front - 650 mm | 480 mm | 650 mm |
| BTC089240 | Pressure Reducing - Closed Front - 650 mm | 480 mm | 650 mm |
| BTC089250 | Pressure Reducing - Custom Size | - | - |
| BTC089131 | Pressure Reducing - Open Front - 460mm - Custom 4HC | - | - |